




SINGLE GANG - RAYNTITE® FLIP COVERS

**One Gang RAYNTITE® Metal Flip Covers - Vertical Mount
20A, 1.710 in. diameter**

D12



Catalog #: 5029-0

APPLICATIONS

For use whenever weatherproof protection is required for an outdoor receptacle.
N/A

PRODUCT FEATURES

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Self closing lids assure weatherproof protection when the receptacle is not in use
- Vertical mount covers padlockable
- May be mounted to box or device
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package

UL LISTED

File E195978

CSA

C22.2 No. 18

NEMA

3R Rated

NEC

2014 Compliant (article 406.9A)

GENERAL PRODUCT INFORMATION

Color: Gray

CONFIGURATION

Gangs: 1

PRODUCT MEASUREMENTS

Wt. Ea. (Lbs.): 0.536

PACKAGING

Package Type: Shrink
 Std. Pkg.: 12
 Product UPC-A Labeled: Yes
 Weight (Lbs. Per/C): 53.60
 Ship Carton Length (in.): 10.56
 Ship Carton Width (in.): 6.50
 Ship Carton Height (in.): 8.50
 Ctn Weight (Lbs.): 6.43
 Pallet Qty: 1680.00
 UPC Number: 050169502907
 I2of5: 50050169502902