




**TWO GANG - RAYNTITE® FLIP COVERS**

**Two Gang RAYNTITE® Metal Flip Covers  
(1) single receptacle, 1.406 in. dia & (1) GFCI**

**D16**



Catalog #: 5040-0

**APPLICATIONS**

For use whenever weatherproof protection is required for an outdoor receptacle.  
N/A

**PRODUCT FEATURES**

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Self closing lids assure weatherproof protection when the receptacle is not in use
- Padlockable, 1/4 in. diameter hole
- May be mounted to box or device
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package

**UL LISTED**

File E195978

**CSA**

C22.2 No. 18

**NEMA**

3R Rated

**NEC**

2014 Compliant (article 406.9A)

**GENERAL PRODUCT INFORMATION**

Color: Gray

**CONFIGURATION**

Gangs: 2

**PRODUCT MEASUREMENTS**

Wt. Ea. (Lbs.): 0.632

**PACKAGING**

Package Type: Shrink  
 Std. Pkg.: 6  
 Product UPC-A Labeled: Yes  
 Weight (Lbs. Per/C): 63.20  
 Ship Carton Length (in.): 10.56  
 Ship Carton Width (in.): 6.50  
 Ship Carton Height (in.): 8.50  
 Ctn Weight (Lbs.): 3.79  
 Pallet Qty: 840.00  
 UPC Number: 050169504000  
 I2of5: 50050169504005