




## 3 IN. X 2 IN. SWITCH BOXES - 1-1/2 TO 2-1/2 IN. DEEP WITH CONDUIT KO'S

2-1/2 in. Deep Switch Boxes - Gangable with Conduit KO's  
TS Bracket, 1/2 in. Setback

A47



Catalog #: 505

### APPLICATIONS

RACO® Switch boxes are used to house wiring devices such as switches and outlets  
N/A

### PRODUCT FEATURES

Gangable switch boxes offer the option of constructing a box to hold two or more devices  
Reference the Box Selection section in the front of this catalog for complete description of bracket types and features

### UL LISTED

File E195978

### COMPLIANCES

All RACO® single gang, two gang, 4 in. square, and single gang gangable UL listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at [www.ul.com](http://www.ul.com)

### FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

### GENERAL PRODUCT INFORMATION

Wiring System: Conduit

### CONFIGURATION

End Knockouts: (2) 3/4 in.  
Ends Cable: ---  
Bracket Type: TS, for Metal or Wood Studs  
Bracket Setback: 1/2 in.  
Side Knockout(s): (2) 1/2 in.  
Bottom Knockouts(s): (2) 1/2 in.

### DRAWING DIMENSIONS

Dimension A: 2-1/2 in.  
Dimension B: 7 in.  
Dimension C: 2-13/64 in.

### PRODUCT MEASUREMENTS

Depth: 2-1/2 in.  
Cubic Inches (cm3): 12.5 (204.8)  
Wt. Ea. (Lbs.): 0.636  
Product Length (in.): 2.50  
Product Width (in.): 7.00  
Product Height (in.): 2.20

### PACKAGING

Minimum Pack Qty.: 50  
Std. Pkg.: 50  
Product UPC-A Labeled: No  
Weight (Lbs. Per/C): 63.60  
Ship Carton Length (in.): 20.00  
Ship Carton Width (in.): 7.50  
Ship Carton Height (in.): 13.50  
Ctn Weight (Lbs.): 31.80  
Pallet Qty: 2100  
UPC Number: 050169005057  
I2of5: 50050169005052