




3 IN. X 2 IN. SWITCH BOXES - 2 TO 3-1/2 IN. DEEP WITH ARMORED CABLE / METAL CLAD / FLEX CLAMPS

2-1/2 in. Deep Switch Boxes - Gangable with Armored Cable/Metal Clad/Flex Clamps
TS Bracket, 1/2 in. Setback

A49



Catalog #: 524

APPLICATIONS

RACO® Switch boxes are used to house wiring devices such as switches and outlets
N/A

PRODUCT FEATURES

Gangable switch boxes offer the option of constructing a box to hold two or more devices
Reference the Box Selection section in the front of this catalog for complete description of bracket types and features

UL LISTED

File E195978

COMPLIANCES

All RACO® single gang, two gang, 4 in. square, and single gang gangable UL listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at www.ul.com

FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

GENERAL PRODUCT INFORMATION

Wiring System: Armored Cable/Metal Clad/MCI-A/Flex

CONFIGURATION

End Knockouts: (2) 1/2 in.
Ends Cable: 4
Bracket Type: TS, for Metal or Wood Studs
Bracket Setback: 1/2 in.
Side Knockout(s): ---
Bottom Knockout(s): (1) 1/2 in.

DRAWING DIMENSIONS

Dimension A: 2-1/2 in.
Dimension B: 7 in.
Dimension C: 2-13/64 in.

PRODUCT MEASUREMENTS

Depth: 2-1/2 in.
Cubic Inches (cm3): 12.5 (204.8)
Wt. Ea. (Lbs.): 0.707
Product Length (in.): 2.50
Product Width (in.): 7.00
Product Height (in.): 2.20

PACKAGING

Minimum Pack Qty.: 50
Std. Pkg.: 50
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 70.70
Ship Carton Length (in.): 20.00
Ship Carton Width (in.): 7.50
Ship Carton Height (in.): 13.50
Ctn Weight (Lbs.): 35.35
Pallet Qty: 2100
UPC Number: 050169905241
I2of5: 50050169905246