


## 3 IN. X 2 IN. SWITCH BOXES - 2-3/4 TO 3-1/2 IN. DEEP WITH CONDUIT KO'S

2-3/4 in. Deep Switch Boxes - Gangable with Conduit KO's Plaster Ears

A48





Catalog #: 560

#### APPLICATIONS

RACO® Switch boxes are used to house wiring devices such as switches and outlets

#### PRODUCT FEATURES

Gangable switch boxes offer the option of constructing a box to hold two or more devices

Plaster ears allow a box to be used in "old work" applications

### UL LISTED

File E195978

#### COMPLIANCES

All RACO® single gang, two gang, 4 in. square, and single gang gangable UL listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at www.ul.com

# FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

## GENERAL PRODUCT INFORMATION

Conduit Wiring System:

CONFIGURATION End Knockouts:

(2) 1/2 in. Ends Cable: No Bracket Bracket Type: Side Knockout(s): (4) 1/2 in. Bottom Knockouts(s) (2) 1/2 in.

DRAWING DIMENSIONS

Dimension A: 2-3/4 in.

PRODUCT MEASUREMENTS

Depth: 2-3/4 in. Cubic Inches (cm3): 14.0 (229.4) Wt. Ea. (Lbs.): 0.595 Product Length (in.): Product Width (in.): 2.75 4.22 Product Height (in.): 2.00

**PACKAGING** 

12of5:

Minimum Pack Qty.: Std. Pkg.: Product UPC-A Labeled: 25 25 Yes Weight (Lbs. Per/C): Ship Carton Length (in.): 59.50 12.38 Ship Carton Width (in.): 6.56 8.75 14.93 Ship Carton Height (in.): Ctn Weight (Lbs.): Pallet Qty: UPC Number: 2250 050169005606

40050169905607