




LAMP HOLDERS

**Traditional Lampholder
75-150 Watt Par 38 Lamps**

D23



Catalog #: 5606-7

APPLICATIONS

For general outdoor lighting in wet, damp or dry locations
May be used with BELL® cluster covers and boxes

PRODUCT FEATURES

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming
- Extra long wire leads for easy hook-up
- Porcelain socket
- Inside Gasket
- Multi-lingual instructions in each package
- 1/2 in. locknut
- N/A

UL LISTED

Standard 1598

CSA

C22.2 No. 18

GENERAL PRODUCT INFORMATION

Color: Bronze

PRODUCT MEASUREMENTS

Wt. Ea. (Lbs.): 0.500

PACKAGING

Package Type:	Carded
Std. Pkg.:	6
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	50.00
Ship Carton Length (in.):	12.13
Ship Carton Width (in.):	11.75
Ship Carton Height (in.):	3.00
Ctn Weight (Lbs.):	3.00
Pallet Qty:	1080.00
UPC Number:	050169560679
I2of5:	50050169560674