


**LAMPHOLDER / COVER COMBOS****4in. Round Cover Combinations for 75-150 Watt Par 38 Lamps
(1) Lampholder / (1) Cover****D25**

Catalog #: 5624-5

APPLICATIONS

For general outdoor lighting in wet, damp or dry locations
 For use with BELL® single gang or round weatherproof boxes

PRODUCT FEATURES

Rugged die cast construction
 State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
 Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming
 Includes gasket and mounting hardware
 Multi-lingual instructions in each package
 No Need to purchase separate components
 N/A

UL LISTED

File E225082

CSA

C22.2 No. 18

GENERAL PRODUCT INFORMATION

Color: Gray

PRODUCT MEASUREMENTS

Wt. Ea. (Lbs.): 0.840

PACKAGING

Package Type:	Carded
Std. Pkg.:	4
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	84.00
Ship Carton Length (in.):	14.19
Ship Carton Width (in.):	6.69
Ship Carton Height (in.):	5.50
Ctn Weight (Lbs.):	3.36
Pallet Qty:	640.00
UPC Number:	050169562451
I2of5:	50050169562456