





LAMPHOLDER / COVER COMBOS

**4in. Round Cover Combinations for 75-150 Watt Par 38 Lamps
(2) Lampholders / (1) Cover**

D25



Catalog #: 5625-5

APPLICATIONS

For general outdoor lighting in wet, damp or dry locations
For use with BELL® single gang or round weatherproof boxes

PRODUCT FEATURES

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package
- No Need to purchase separate components
- N/A

UL LISTED

File E225082

CSA

C22.2 No. 18

GENERAL PRODUCT INFORMATION

Color: Gray

PRODUCT MEASUREMENTS

Wt. Ea. (Lbs.): 1.188

PACKAGING

Package Type:	Carded
Std. Pkg.:	4
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	118.80
Ship Carton Length (in.):	14.19
Ship Carton Width (in.):	6.69
Ship Carton Height (in.):	5.50
Ctn Weight (Lbs.):	4.75
Pallet Qty:	640.00
UPC Number:	050169562550
I2of5:	50050169562555