

15 kV, 600 Amp ETP Kit w/ Test Point

by Hubbell Power Systems
Catalog ID: 615ETPM38T

15 kV 600 Amp Elbow Tap Plug Kit with Test Point. Cable insulation range 1.370 in - 1.630 in. Kit includes T-body, insulating plug with cap, 750 compression lug, threaded stud, and cable adapter



* Representative image

Product Details

General

Connector Type	Aluminum
Type	600 Amp Dead Break
UPC	096359391647
With Seal Kit	No
With Test Point	Yes

Dimensions

Cable Insulation Diameter Maximum	1.630 in
Cable Insulation Diameter Minimum	1.370 in
Weight	8.650 lb

Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	600 A
kV Class	15 kV

Conductor Related

Cable Insulation Diameter Range	1.370 - 1.630
Solid or Compacted Conductor	900
Stranded or Compressed Conductor	700/750

Logistics

Pallet Quantity	64 EA
-----------------	-------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com