



# 15 kV LRTP Kit w/ Test Point and Jacket Seal Kit

by Hubbell Power Systems  
Catalog ID: 615LRTPH27TJ

15 kV 600 Amp Load Break Reducing Tap Plug Kit with Test Point. Cable insulation range 0.850 in - 1.050 in. Kit includes T-body, insulating plug with cap, compression lug, threaded stud, and cable adapter



\* Representative image

## Product Details

### General

Connector Type	Aluminum Threaded
Type	600 Amp Dead Break
UPC	096359437772
With Seal Kit	Yes
With Test Point	Yes

### Dimensions

Cable Insulation Diameter Maximum	1.050 in
Cable Insulation Diameter Minimum	0.850 in
Weight	10.000 lb

### Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	600 A
kV Class	15 kV

### Conductor Related

Cable Insulation Diameter Range	0.850 - 1.050
Solid or Compacted Conductor	250
Stranded or Compressed Conductor	4/0

### Logistics

Pallet Quantity	64 EA
-----------------	-------

**For further technical assistance, please contact us**

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)