



# 25/28 kV, 600 Amp, T-Body Kit

by Hubbell Power Systems  
Catalog ID: 625BTH26

25/28 kV 600 Amp T-Body Kit. Cable insulation range 0.850 in - 1.050 in.  
Kit includes T-body, insulating plug with cap, 3/0 compression lug, threaded stud, and cable adapter



\* Representative image

## Product Details

### General

Connector Type	Aluminum
Type	600 Amp Dead Break
UPC	096359437901
With Seal Kit	No
With Test Point	No

### Dimensions

Cable Insulation Diameter Maximum	1.050 in
Cable Insulation Diameter Minimum	0.850 in
Weight	8.150 lb

### Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	600 A
kV Class	25/28 kV

### Conductor Related

Cable Insulation Diameter Range	0.850 - 1.050
Solid or Compacted Conductor	4/0
Stranded or Compressed Conductor	3/0

### Logistics

Pallet Quantity	64 EA
Standard Package	1

**For further technical assistance, please contact us**

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)