



25/28 kV, 600 Amp, T-Body Kit

by Hubbell Power Systems
Catalog ID: 625BTH30

25/28 kV 600 Amp T-Body Kit. Cable insulation range 0.850 in - 1.050 in.
Kit includes T-body, insulating plug with cap, 350 compression lug, threaded stud, and cable adapter



* Representative image

Product Details

General

Connector Type	Aluminum
Type	600 Amp Dead Break
UPC	096359391821
With Seal Kit	No
With Test Point	No

Dimensions

Cable Insulation Diameter Maximum	1.050 in
Cable Insulation Diameter Minimum	0.850 in
Weight	8.150 lb

Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	600 A
kV Class	25/28 kV

Conductor Related

Cable Insulation Diameter Range	0.850 - 1.050
Solid or Compacted Conductor	400
Stranded or Compressed Conductor	350

Logistics

Pallet Quantity	64 EA
-----------------	-------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com