



* Representative image

25/28 kV, 600 Amp, T-Body Kit, w/ Jacket Seal kit

by Hubbell Power Systems
Catalog ID: 625BTJ27J

25/28 kV 600 Amp T-Body Kit. Cable insulation range 0.980 in - 1.180 in. Kit includes T-body, insulating plug with cap, 4/0 compression lug, threaded stud, cable adapter, and seal kit

Product Details

General

Connector Type	Aluminum
Type	600 Amp Dead Break
UPC	096359437925
With Seal Kit	Yes
With Test Point	No

Dimensions

Cable Insulation Diameter Maximum	1.180 in
Cable Insulation Diameter Minimum	0.980 in
Weight	8.650 lb

Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	600 A
kV Class	25/28 kV

Conductor Related

Cable Insulation Diameter Range	0.980 - 1.180
Solid or Compacted Conductor	250
Stranded or Compressed Conductor	4/0

Logistics

Pallet Quantity	64 EA
-----------------	-------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com