

Anchor, Tool, Kelly Bar Adapter, 2.5in Square, 10,000 ft-lb rating

by CHANCE Utility
Catalog ID: 630017

Standard Kelly Bar Adapter 10,000 Ft Lbs (13,558 N-M) for 2 1/2" (63.5 mm) Square Kelly Bar.

- Kelly Bar Adapter attaches to truck's torque motor drive shaft (Kelly Bar)
- Locking Dog Assembly has six holes for 1/2" bolts on a 5-1/4" bolt circle, comes with six 1/2" Grade 5 bolts, nuts and lock washers
- Painted with green paint



* Representative image

Product Details

General

Bolt Grade	5
Kelly Bar Shape	Square
Number of Bolt Holes	6
Torque Rating	10000 ft-lbs
Type	Anchor/Pile Installation Tools
UPC	096359227489

Dimensions

Anchor Installation Hole Size	0.5 in
Diameter - Bolt	0.5 in
Diameter - Bolt Circle	5.25 in
Kelly Bar Adapter Inside Width	2.5 in
Kelly Bar Hole Distance to Flange	2.25 in
Length	3.500 in
Weight	8.820 lb

Logistics

Pallet Quantity	90 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com