



* Representative image

Anchor, No Wrench, 6in x 66in Tripleye

by CHANCE Utility
Catalog ID: 6346

No-Wrench 66" (1676 mm) long with 6" (152 mm) Helix Tripleye.

- No-Wrench Screw Anchors may be installed by hand or machine.
- Hot dipped galvanized per ASTM A153
- No-Wrench Screw Anchors can be installed to a greater depth to reach a firmer soil by using an extension rod

Product Details

General

Coating	Galvanized
Eyenuit Style	Tripleye
Number of Helices	1
Torque Rating	400 ft-lbs
Type	Helical Anchors
UPC	096359072980

Dimensions

Anchor Helix Diameter(s)	6 in
Length	66.000 in
Rod Diameter	0.750 in
Weight	11.270 lb

Certifications and Compliance

Industry Standard(s)	RUS Accepted
----------------------	--------------

Logistics

Pallet Quantity	100 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com