


**SINGLE DEVICE HANDY BOXES & COVERS****3-3/4 in. x 1-9/16 in. Industrial Handy Box and Cover - Drawn with Conduit KO's  
1-1/2 in. Depth****A45**

Catalog #: 640

**APPLICATIONS**

RACO® Handy boxes, also called utility boxes, are used for convenience outlets, switch boxes or small junction boxes. They are popular for exposed work applications (surface mounted wiring). The NEC requires that surface-mounted wiring be enclosed with a protective covering such as EMT conduit.

**PRODUCT FEATURES**

RACO® Handy Box covers are designed to match the contours of the box.

**UL LISTED**

File E195978

**FIRE RESISTANCE**

Acceptable for use in 2-hour rated walls.

**GENERAL PRODUCT INFORMATION**

Wiring System: Conduit

**CONFIGURATION**

End Knockouts: (2) 1/2 in.  
Bracket Type: No Bracket  
Drawn or Welded: Drawn  
Raised Ground: No  
Side Knockout(s): (6) 1/2 in.  
Bottom Knockouts(s): (3) 1/2 in.

**DRAWING DIMENSIONS**

Dimension A: 1-1/2 in.

**PRODUCT MEASUREMENTS**

Depth: 1-1/2 in.  
Cubic Inches (cm3): 7.3 (119.6)  
Wt. Ea. (Lbs.): 0.331  
Product Length (in.): 1.56  
Product Width (in.): 3.75  
Product Height (in.): 1.56

**PACKAGING**

Minimum Pack Qty.: 50  
Std. Pkg.: 50  
Product UPC-A Labeled: No  
Weight (Lbs. Per/C): 33.10  
Ship Carton Length (in.): 11.50  
Ship Carton Width (in.): 5.00  
Ship Carton Height (in.): 9.25  
Ctn Weight (Lbs.): 16.55  
Pallet Qty: 7200  
UPC Number: 050169006405  
I2of5: 50050169006400