




SINGLE DEVICE HANDY BOXES & EXTENSION RINGS

4 in. x 2 in. Handy Boxes, 1-1/2 in. Deep - Welded with Conduit KO's
B Bracket, 1/4 in. Setback

A44



Catalog #: 655

APPLICATIONS

RACO® Handy boxes, also called utility boxes, are used for convenience outlets, switch boxes or small junction boxes
N/A

UL LISTED

File E195978

COMPLIANCES

All RACO® single gang, two gang, 4 in. square, and single gang gangable UL listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at www.ul.com

FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

GENERAL PRODUCT INFORMATION

Wiring System: Conduit

CONFIGURATION

End Knockouts: (2) 1/2 in.
Bracket Type: B, for Wood Studs
Bracket Setback: 1/4 in.
Drawn or Welded: Welded
Raised Ground: No
Side Knockout(s): (3) 1/2 in.
Bottom Knockouts(s): (3) 1/2 in.

DRAWING DIMENSIONS

Dimension A: 1-1/2 in.
Dimension B: 1-31/32 in.
Dimension C: 4-1/8 in.

PRODUCT MEASUREMENTS

Depth: 1-1/2 in.
Cubic Inches (cm3): 11.5 (188.5)
Wt. Ea. (Lbs.): 0.542
Product Length (in.): 1.56
Product Width (in.): 4.00
Product Height (in.): 4.00

PACKAGING

Minimum Pack Qty.: 50
Std. Pkg.: 50
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 54.20
Ship Carton Length (in.): 18.75
Ship Carton Width (in.): 8.88
Ship Carton Height (in.): 7.38
Ctn Weight (Lbs.): 27.10
Pallet Qty: 3500
UPC Number: 050169006559
I2of5: 50050169006554