




SINGLE DEVICE HANDY BOXES & EXTENSION RINGS

4 in. x 2 in. Handy Boxes, 1-7/8 in. Deep - Drawn with Conduit KO's
Raised Ground, TS Bracket, 1/2 in. Setback

A44



Catalog #: 662SP

APPLICATIONS

RACO® Handy boxes, also called utility boxes, are used for convenience outlets, switch boxes or small junction boxes. They are popular for exposed work applications (surface mounted wiring). The NEC requires that surface-mounted wiring be enclosed with a protective covering such as EMT conduit.

PRODUCT FEATURES

Reference the Box Selection section in the front of this catalog for complete description of bracket types and features
N/A

COMPLIANCES

All RACO® single gang, two gang, 4 in. square, and single gang gangable UL listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at www.ul.com

FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

GENERAL PRODUCT INFORMATION

Wiring System: Conduit

CONFIGURATION

End Knockouts: (2) 1/2 in.
Bracket Type: TS, for Metal or Wood Studs
Bracket Setback: 1/2 in.
Drawn or Welded: Drawn
Raised Ground: Yes
Side Knockout(s): (3) 1/2 in.
Bottom Knockouts(s): (3) 1/2 in.

DRAWING DIMENSIONS

Dimension A: 1-7/8 in.
Dimension B: 7 in.
Dimension C: 2-3/8 in.

PRODUCT MEASUREMENTS

Depth: 1-7/8 in.
Cubic Inches (cm³): 13.0 (213.0)
Wt. Ea. (Lbs.): 0.608
Product Length (in.): 1.94
Product Width (in.): 7.00
Product Height (in.): 2.38

PACKAGING

Minimum Pack Qty.: 18
Std. Pkg.: 18
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 60.80
Ship Carton Length (in.): 17.75
Ship Carton Width (in.): 6.00
Ship Carton Height (in.): 7.50
Ctn Weight (Lbs.): 10.95
Pallet Qty: 1728
UPC Number: 050169006627
I2of5: 50050169106629