




SINGLE DEVICE HANDY BOXES & EXTENSION RINGS

4 in. x 2 in. Handy Boxes, 1-7/8 in. Deep - Drawn with Conduit KO's
Raised Ground, 10 in. #12 Stranded Copper Pigtail

A44



Catalog #: 663SM

APPLICATIONS

RACO® Handy boxes, also called utility boxes, are used for convenience outlets, switch boxes or small junction boxes. They are popular for exposed work applications (surface mounted wiring). The NEC requires that surface-mounted wiring be enclosed with a protective covering such as EMT conduit.

PRODUCT FEATURES

N/A

UL LISTED

File E195978

COMPLIANCES

All RACO® single gang, two gang, 4 in. square, and single gang gangable UL listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at www.ul.com

FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

GENERAL PRODUCT INFORMATION

Wiring System: Conduit

CONFIGURATION

End Knockouts: (2) 3/4 in.
Bracket Type: No Bracket
Drawn or Welded: Drawn
Raised Ground: Yes
Side Knockout(s): (4) 3/4 in.
Bottom Knockouts(s): (1) 3/4 in.

DRAWING DIMENSIONS

Dimension A: 1-7/8 in.

PRODUCT MEASUREMENTS

Depth: 1-7/8 in.
Cubic Inches (cm3): 13.0 (213.0)
Wt. Ea. (Lbs.): 0.518
Product Length (in.): 1.94
Product Width (in.): 4.00
Product Height (in.): 2.13

PACKAGING

Minimum Pack Qty.: 50
Std. Pkg.: 50
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 51.80
Ship Carton Length (in.): 11.13
Ship Carton Width (in.): 8.50
Ship Carton Height (in.): 10.00
Ctn Weight (Lbs.): 25.90
Pallet Qty: 4000
UPC Number: 050169986639
I2of5: 50050169986634