




SINGLE DEVICE HANDY BOXES & COVERS

4 in. x 2 in. Handy Boxes, 2-1/8 in. Deep - Welded with Conduit KO's

A45



Catalog #: 670RAC

APPLICATIONS

RACO® Handy boxes, also called utility boxes, are used for convenience outlets, switch boxes or small junction boxes
N/A

UL LISTED

File E195978

FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

GENERAL PRODUCT INFORMATION

Wiring System: Conduit

CONFIGURATION

End Knockouts:	(2) 1/2 in.
Bracket Type:	No Bracket
Drawn or Welded:	Welded
Raised Ground:	No
Side Knockout(s):	(6) 1/2 in.
Bottom Knockouts(s):	(3) 1/2 in.

DRAWING DIMENSIONS

Dimension A: 2-1/8 in.

PRODUCT MEASUREMENTS

Depth:	2-1/8 in.
Cubic Inches (cm3):	16.5 (270.4)
Wt. Ea. (Lbs.):	0.615
Product Length (in.):	2.19
Product Width (in.):	4.00
Product Height (in.):	2.13

PACKAGING

Minimum Pack Qty.:	50
Std. Pkg.:	50
Product UPC-A Labeled:	No
Weight (Lbs. Per/C):	61.50
Ship Carton Length (in.):	12.13
Ship Carton Width (in.):	10.50
Ship Carton Height (in.):	9.44
Ctn Weight (Lbs.):	30.75
Pallet Qty:	3200
UPC Number:	050169906705
I2of5:	50050169906700