




SINGLE DEVICE HANDY BOXES & COVERS

4 in. x 2 in. Handy Boxes, 2-1/8 in. Deep - Welded with Conduit KO's
A Bracket, 5/8 in. Setback

A45



Catalog #: 671

APPLICATIONS

RACO® Handy boxes, also called utility boxes, are used for convenience outlets, switch boxes or small junction boxes
N/A

PRODUCT FEATURES

Reference the Box Selection section in the front of this catalog for complete description of bracket types and features

UL LISTED

File E195978

FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

GENERAL PRODUCT INFORMATION

Wiring System: Conduit

CONFIGURATION

End Knockouts: (2) 1/2 in.
Bracket Type: A, for Metal or Wood Studs
Bracket Setback: 5/8 in.
Drawn or Welded: Welded
Raised Ground: No
Side Knockout(s): (3) 1/2 in.
Bottom Knockouts(s): (3) 1/2 in.

DRAWING DIMENSIONS

Dimension A: 2-1/8 in.
Dimension B: 6-7/16 in.
Dimension C: 2-7/32 in.

PRODUCT MEASUREMENTS

Depth: 2-1/8 in.
Cubic Inches (cm³): 16.5 (270.4)
Wt. Ea. (Lbs.): 0.787
Product Length (in.): 2.19
Product Width (in.): 6.44
Product Height (in.): 2.34

PACKAGING

Minimum Pack Qty.: 50
Std. Pkg.: 50
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 78.70
Ship Carton Length (in.): 20.25
Ship Carton Width (in.): 8.50
Ship Carton Height (in.): 10.25
Ctn Weight (Lbs.): 39.35
Pallet Qty.: 2500
UPC Number: 050169006719
I2of5: 30050169006710