




## TWO DEVICE HANDY / SWITCH BOXES & COVERS

4 in. Square Two Device Switch Boxes, 2-1/8 in. Deep - Drawn with Conduit KO's  
TS Bracket, 1/2 in. Setback

A46



Catalog #: 681

### APPLICATIONS

Installers can save time and cut installation costs with two gang switch boxes  
Larger capacity boxes are ideal for today's designs where there is a need to install two devices at one location

### PRODUCT FEATURES

Reference the Box Selection section in the front of this catalog for complete description of bracket types and features  
681, 685 bracketed boxes are set back 1/2" eliminating the need for a plaster ring  
N/A

### UL LISTED

File E195978

### COMPLIANCES

All RACO® single gang, two gang, 4 in. square, and single gang gangable UL listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at [www.ul.com](http://www.ul.com)

### FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

### GENERAL PRODUCT INFORMATION

Wiring System: Conduit

### CONFIGURATION

Bracket Type: TS, for Metal or Wood Studs  
Bracket Setback: 1/2 in.  
Drawn or Welded: Drawn  
Raised Ground: No  
Side Knockout(s): (9) 1/2 in.  
Bottom Knockouts(s): (5) 1/2 in.

### DRAWING DIMENSIONS

Dimension A: 2-1/8 in.  
Dimension B: 4 in.  
Dimension C: 4 in.  
Dimension D: 7 in.  
Dimension E: 4-9/32 in.

### PRODUCT MEASUREMENTS

Depth: 2-1/8 in.  
Cubic Inches (cm3): 30.3 (496.5)  
Wt. Ea. (Lbs.): 0.926  
Product Length (in.): 2.19  
Product Width (in.): 7.00  
Product Height (in.): 4.38

### PACKAGING

Minimum Pack Qty.: 25  
Std. Pkg.: 25  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 92.60  
Ship Carton Length (in.): 20.25  
Ship Carton Width (in.): 7.38  
Ship Carton Height (in.): 9.88  
Ctn Weight (Lbs.): 23.15  
Pallet Qty: 1200  
UPC Number: 050169006818  
I2of5: 50050169006813