




TWO DEVICE HANDY / SWITCH BOXES & COVERS

4 in. Square Two Device Switch Boxes, 2-1/8 in. Deep - Drawn with Conduit KO's

A46



Catalog #: 683

APPLICATIONS

Installers can save time and cut installation costs with two gang switch boxes. Larger capacity boxes are ideal for today's designs where there is a need to install two devices at one location. Drawn boxes are ideal for exposed work applications (surface mounted wiring).

PRODUCT FEATURES

N/A

UL LISTED

File E195978

COMPLIANCES

All RACO® single gang, two gang, 4 in. square, and single gang gangable UL listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at www.ul.com

FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

GENERAL PRODUCT INFORMATION

Wiring System: Conduit

CONFIGURATION

Bracket Type: No Bracket
Drawn or Welded: Drawn
Raised Ground: No
Side Knockout(s): (8) 1/2 in. & (4) 3/4 in.
Bottom Knockouts(s): (3) 1/2 in. & (2) 3/4 in.

DRAWING DIMENSIONS

Dimension A: 2-1/8 in.
Dimension B: 4 in.
Dimension C: 4 in.

PRODUCT MEASUREMENTS

Depth: 2-1/8 in.
Cubic Inches (cm3): 30.3 (496.5)
Wt. Ea. (Lbs.): 0.816
Product Length (in.): 2.19
Product Width (in.): 4.00
Product Height (in.): 4.00

PACKAGING

Minimum Pack Qty.: 25
Std. Pkg.: 25
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 81.60
Ship Carton Length (in.): 18.75
Ship Carton Width (in.): 8.88
Ship Carton Height (in.): 7.38
Ctn Weight (Lbs.): 20.40
Pallet Qty: 1750
UPC Number: 050169006832
I2of5: 50050169006837