



MASONRY BOXES & SUPPORTS

**Block-Loc Masonry Boxes, 3-1/2" Deep - Nongangable with Conduit KO's
2 Gang, Welded**

A59



Catalog #: 696B

APPLICATIONS

For power and data outlets in masonry block walls
Secures masonry box in block wall and prevents box from moving during construction

PRODUCT FEATURES

Integral brackets securely hold box to concrete block from front and back in masonry block walls, even in irregular openings
Quick and accurate positioning
Break off front tabs

UL LISTED

File E195978

CULUS

N/A

COMPLIANCES

They are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at www.ul.com

FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

GENERAL PRODUCT INFORMATION

Wiring System: Conduit
Color: Gray

CONFIGURATION

End Knockouts: (8) 1/2" - 3/4" Conc. KO
Drawn or Welded: Welded
Raised Ground: No
Gangs: 2
Side Knockout(s): (4) 1/2" - 3/4" Conc. KO
Bottom Knockouts(s): (4) 1/2" - 3/4" Conc. KO

PRODUCT MEASUREMENTS

Depth: 3-1/2 in.
Cubic Inches (cm3): 45.0
Wt. Ea. (Lbs.): 1.326
Product Length (in.): 3.578
Product Width (in.): 5.359
Product Height (in.): 3.797

PACKAGING

Package Type: Boxed
Minimum Pack Qty.: 12
Std. Pkg.: 12
Ship Carton Qty.: 12
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 132.600
Ship Carton Length (in.): 11.380
Ship Carton Width (in.): 10.630
Ship Carton Height (in.): 8.250
Ctn Weight (Lbs.): 15.912
Pallet Qty: 960
UPC Number: 050169500637
I2of5: 50050169500632