




## MASONRY BOXES & PARTITIONS

Masonry Boxes, 3-1/2 in. Deep - Nongangable with Conduit KO's  
5-Gang, 9-7/32 in. Wide

A58



Catalog #: 699

### APPLICATIONS

RACO® Masonry boxes are designed to accommodate the mounting of switches or other devices in masonry walls  
2-1/2" deep boxes are used in 4" block walls, 3-1/2" deep boxes are used in 6" or 8" block walls

### PRODUCT FEATURES

- Rugged welded design does not fall apart during construction
- Available from one to six gang configurations in both 2-1/2" and 3-1/2" depths
- Rectangular shape fits square cuts in block
- Large volume design allows for additional work room inside the box
- Standard 1/2" and 3/4" concentric knockouts
- Device ears inside the box prevent mortar from getting in the device holes
- Steel voltage partition #971 fits all 2-1/2" or 3-1/2" depths
- Standard wall plates can be used
- N/A

### UL LISTED

File E195978

### GENERAL PRODUCT INFORMATION

Wiring System: Conduit

### CONFIGURATION

End Knockouts: 20 Conc.  
 Drawn or Welded: Welded  
 Gangs: 5  
 Side Knockout(s): 15 Conc.  
 Bottom Knockouts(s): 5 Conc.

### DRAWING DIMENSIONS

Dimension A: 3-1/2 in.  
 Dimension B: 9-7/32 in.

### PRODUCT MEASUREMENTS

Depth: 3-1/2 in.  
 Cubic Inches (cm3): 112.3 (1840.2)  
 Wt. Ea. (Lbs.): 2.230  
 Product Length (in.): 3.50  
 Product Width (in.): 3.75  
 Product Height (in.): 9.22

### PACKAGING

Minimum Pack Qty.: 10  
 Std. Pkg.: 10  
 Product UPC-A Labeled: No  
 Weight (Lbs. Per/C): 223.00  
 Ship Carton Length (in.): 21.38  
 Ship Carton Width (in.): 7.50  
 Ship Carton Height (in.): 9.75  
 Ctn Weight (Lbs.): 22.30  
 Pallet Qty: 600  
 UPC Number: 050169006993  
 I2of5: 50050169006998