




OLD WORK NON-METALLIC CABLE BOXES

Old Work Cable Boxes - For Nonmetallic Sheathed Cable
3-1/2 in. Round, 2-13/16 in. Deep, 18.0 Cu. in., Flush Mount

A78



Catalog #: 7122RAC

APPLICATIONS

RACO® Nonmetallic cable boxes are used in branch circuit wiring to splice wires
Accommodates wiring devices such as switches and receptacles
Provide excellent protection for wiring system or devices

PRODUCT FEATURES

RACO® Nonmetallic cable boxes provide the installer with a cost alternative that is lightweight and easy to install
Self-clamping wire entry clamps
Extra long, metal swing arms ensure installation
Wrap around metal clamp to secure box to sheet rock

UL LISTED

File E 195963

COMPLIANCES

Boxes are listed for Applications (Electrical Codes), UL Green Book
Boxes are listed for mechanical properties, including the 2-hour Fire Rating, (building codes) UL Orange Book
Federal Manufacturer's number 28488

US PATENTS

4,183,486; 4,874,905; 4,580,689; 4,666,599

OTHER PATENTS

Canada 1,237,515; 1,260,599

GENERAL PRODUCT INFORMATION

Wiring System: Nonmetallic Sheathed Cable
Color: Gray

RECOMMENDED MAX LOAD

Fixture (Static) Lbs.: 6

CONFIGURATION

Cable Clamps: 4

DRAWING DIMENSIONS

Dimension A: 2-13/16 in.

PRODUCT MEASUREMENTS

Depth: 2-13/16 in.
Cubic Inches (cm3): 18.0 (295.0)
Wt. Ea. (Lbs.): 0.225
Product Length (in.): 2.81
Product Width (in.): 4.38
Product Height (in.): 4.38

PACKAGING

Minimum Pack Qty.: 100
Std. Pkg.: 100
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 22.50
Ship Carton Length (in.): 24.00
Ship Carton Width (in.): 15.00
Ship Carton Height (in.): 16.00
Ctn Weight (Lbs.): 22.10
Pallet Qty: 1000
UPC Number: 050169971222
I2of5: 50050169971227

