




## SINGLE GANG NON-METALLIC CABLE BOXES - WITH CAPTIVE NAILS

Single-gang with Captive Nails - For Nonmetallic Sheathed Cable  
2-3/4 in. Deep, 18.0 Cu. in., Nails, 1/2 in. Setback

A75



Catalog #: 7302RAC

### APPLICATIONS

RACO® Nonmetallic cable boxes are used in branch circuit wiring to splice wires  
Accommodates wiring devices such as switches and receptacles  
Provide excellent protection for wiring system or devices

### PRODUCT FEATURES

RACO® Nonmetallic cable boxes provide the installer with a cost alternative that is lightweight and easy to install  
Single-gang boxes have knockouts that break out quickly and cleanly for faster installation  
Positioning tabs for fast accurate mounting on studs or joists  
Oversized nail support that resists hammer impact and prevents box deformation

### UL LISTED

File E 195963

### COMPLIANCES

Boxes are listed for Applications (Electrical Codes), UL Green Book  
Boxes are listed for mechanical properties, including the 2-hour Fire Rating, (building codes) UL Orange Book  
Federal Manufacturer's number 28488

### FIRE RESISTANCE

2-hour fire rating, UL Orange Book

### GENERAL PRODUCT INFORMATION

Wiring System: Nonmetallic Sheathed Cable  
Color: Gray

### CONFIGURATION

Cable Knockouts(s): 4

### DRAWING DIMENSIONS

Dimension A: 2-3/4 in.  
Dimension C: 3-19/32 in.  
Dimension D: 1/2 in.

### PRODUCT MEASUREMENTS

Depth: 2-3/4 in.  
Cubic Inches (cm<sup>3</sup>): 18.0 (295.0)  
Wt. Ea. (Lbs.): 0.220  
Product Length (in.): 2.75  
Product Width (in.): 3.84  
Product Height (in.): 2.25

### PACKAGING

Minimum Pack Qty.: 100  
Std. Pkg.: 100  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 22.00  
Ship Carton Length (in.): 24.00  
Ship Carton Width (in.): 12.00  
Ship Carton Height (in.): 16.00  
Ctn Weight (Lbs.): 21.95  
Pallet Qty: 2400  
UPC Number: 050169973028  
I2of5: 50050169973023