


**SINGLE GANG NON-METALLIC CABLE BOXES - BRACKETED**

Single-gang with Brackets for Metal or Wood Studs - For Nonmetallic sheathed Cable
 1-1/4 in. Deep, 8.0 Cu. in., Flanged, 3/8 in. Setback

A77



Catalog #: 7318RAC

APPLICATIONS

RACO® Nonmetallic cable boxes are used in branch circuit wiring to splice wires
 Accommodates wiring devices such as switches and receptacles
 Provide excellent protection for wiring system or devices

PRODUCT FEATURES

RACO® Nonmetallic cable boxes provide the installer with a cost alternative that is lightweight and easy to install
 Single-gang boxes have knockouts that break out quickly and cleanly for faster installation
 Positioning tabs for fast accurate mounting on studs or joists

UL LISTED

File E195963

COMPLIANCES

Boxes are listed for Applications (Electrical Codes), UL Green Book
 Boxes are listed for mechanical properties, including the 2-hour Fire Rating, (building codes) UL Orange Book
 Federal Manufacturer's number 28488

FIRE RESISTANCE

2-hour fire rating, UL Orange Book

US PATENTS

4,580,689; 4,666,055

OTHER PATENTS

Canada 1,237,515; 1,260,599

GENERAL PRODUCT INFORMATION

Wiring System: Nonmetallic Sheathed Cable
 Color: Gray

CONFIGURATION

Cable Knockouts(s): 2
 Bracket Setback: 3/8 in.

DRAWING DIMENSIONS

Dimension A: 1-1/4 in.
 Dimension C: 3-1/2 in.

PRODUCT MEASUREMENTS

Depth: 1-1/4 in.
 Cubic Inches (cm3): 8.0 (131.0)
 Wt. Ea. (Lbs.): 0.104
 Product Length (in.): 1.25
 Product Width (in.): 4.00
 Product Height (in.): 2.38

PACKAGING

Minimum Pack Qty.: 25
 Std. Pkg.: 25
 Product UPC-A Labeled: Yes
 Weight (Lbs. Per/C): 10.40
 Ship Carton Length (in.): 12.00
 Ship Carton Width (in.): 8.94
 Ship Carton Height (in.): 12.00
 Ctn Weight (Lbs.): 2.60

Pallet Qty:
UPC Number:
I2of5:

1500
050169973189
50050169973184