



4 IN. SQUARE FIXTURE COVERS

4 in. Square Fixture Covers
Raised 5/8 in., Open Ears 2-3/4 in. O.C.

A22.1



Catalog #: 756

APPLICATIONS

Raised fixture covers are used where fixtures will be installed

PRODUCT FEATURES

Angled mounting slots compensate up to 12 degrees for box misalignment

UL LISTED

File E195978

CSA

File LR-1082

COMPLIANCES

MSDS
www.hubbell-rtb.com/certifications/Hubbell-RACO_MSDS_for_Steel_Boxes_and_Covers.pdf

GENERAL PRODUCT INFORMATION

RECOMMENDED MAX LOAD

Ceiling Fan (Dynamic) Lbs.:	No
Fixture (Static) Lbs.:	50

CONFIGURATION

Raised (in.): 5/8 in.

PRODUCT MEASUREMENTS

Cubic Inches (cm3):	4.0 (65.5)
Wt. Ea. (Lbs.):	0.245
Product Length (in.):	0.63
Product Width (in.):	4.00
Product Height (in.):	4.00

PACKAGING

Minimum Pack Qty.:	100
Std. Pkg.:	100
Product UPC-A Labeled:	No
Weight (Lbs. Per/C):	24.50
Ship Carton Length (in.):	11.38
Ship Carton Width (in.):	8.25
Ship Carton Height (in.):	10.63
Ctn Weight (Lbs.):	24.45
Pallet Qty:	8000
UPC Number:	050169907566
I2of5:	50050169907561