




## SINGLE GANG NON-METALLIC CABLE BOXES - BRACKETED

Single-gang with Brackets for Metal or Wood Studs - For Nonmetallic sheathed Cable  
2-27/32 in. Deep, 20.0 Cu. in., Face Mount, 1/2 in. Setback

A77



Catalog #: 7717RAC

### APPLICATIONS

RACO® Nonmetallic cable boxes are used in branch circuit wiring to splice wires  
Accommodates wiring devices such as switches and receptacles  
Provide excellent protection for wiring system or devices

### PRODUCT FEATURES

RACO® Nonmetallic cable boxes provide the installer with a cost alternative that is lightweight and easy to install  
Single-gang boxes have knockouts that break out quickly and cleanly for faster installation  
Positioning tabs for fast accurate mounting on studs or joists

### UL LISTED

File E195963

### COMPLIANCES

Boxes are listed for Applications (Electrical Codes), UL Green Book  
Boxes are listed for mechanical properties, including the 2-hour Fire Rating, (building codes) UL Orange Book  
Federal Manufacturer's number 28488

### FIRE RESISTANCE

2-hour fire rating, UL Orange Book

### US PATENTS

4,580,689; 4,666,055

### OTHER PATENTS

Canada 1,237,515; 1,260,599

### GENERAL PRODUCT INFORMATION

Wiring System: Nonmetallic Sheathed Cable  
Color: Gray

### CONFIGURATION

Cable Knockouts(s): 4  
Bracket Type: Face Mount  
Bracket Setback: 1/2 in.

### DRAWING DIMENSIONS

Dimension A: 2-27/32 in.  
Dimension C: 3-19/32 in.  
Dimension D: 1/2 in.

### PRODUCT MEASUREMENTS

Depth: 2-27/32 in.  
Cubic Inches (cm<sup>3</sup>): 20.0 (327.7)  
Wt. Ea. (Lbs.): 0.182  
Product Length (in.): 2.84  
Product Width (in.): 3.59  
Product Height (in.): 3.38

### PACKAGING

Minimum Pack Qty.: 100  
Std. Pkg.: 100  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 18.20  
Ship Carton Length (in.): 24.00  
Ship Carton Width (in.): 15.00

Ship Carton Height (in.):	16.00
Ctn Weight (Lbs.):	18.20
Pallet Qty:	1000
UPC Number:	050169977170
I2of5:	50050169977175