



# Strain Clamp, Snubbing

by ANDERSON  
Catalog ID: 785002000

Strain Clamp, Snubbing, Ductile Iron, Static Wire Range 0.16 - 0.55 in,  
Fitting: None

## Product Details

### General

Bolt Installation Torque (Recommended)	0 ft-lbs
Fitting Type	None
Material	Ductile Iron
Number of Pad Holes	0
Product Category	Strain Clamp
Strength Rating - Ultimate Body	14000 lb
Tension Range	0 lb
Type	Bolted
UPC	096359252252

### Dimensions

Actual Clamp Strand Diameter Range	0 in
Adjustment Step	0 in
Angle - Pad	0 °
Clamping - Maximum	0 in
Clamping - Minimum	0 in
Diameter - Clamping Hardware	0 in
Diameter - Clevis Pin	0 in
Diameter - Eye Hole	0 in
Diameter - Inside	0 in
Diameter - Pad Bolt	0 in
Length - Pin	0 in
Take Up	0 in
Thickness - Pad	0 in
Total Adjustment	0 in
Weight	3.820 lb

### Conductor Related

Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter - Maximum	0.55 in

Conductor Diameter - Minimum	0.16 in
Conductor Diameter Range	0.16 - 0.55
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

## Logistics

Pallet Quantity	270 EA
-----------------	--------

**For further technical assistance, please contact us**

### **Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsh@hubbell.com](mailto:hpscsh@hubbell.com)

### **International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)