



*Commercial, Industrial
and Residential Electrical Products*

4 In. Square Box, Welded, 1-1/2 In. Deep with Nine 1/2 In. KO's and Five TKO's, FH Flush Bracket

Catalog #:
8197



FEATURE BENEFIT

Designed to enclose electrical wiring, switches, receptacles or lighting fixtures. Constructed from 1/16 In. pre-galvanized steel. 8-32 cover mounting screws assembled.

PRODUCT FEATURES

- TKO knockout design provides installation flexibility
- FH style bracket, flush
- Welded construction
- Nine 1/2 In. knockouts and Five TKO knockouts
- 21.0 Cu. In. capacity
- Acceptable in 2-hour fire rated walls

APPLICATIONS

Suitable for use without a bonding jumper in circuits up to 600V.

CERTIFICATIONS



PRODUCT SPECIFICATIONS

UPC Number:	050169001974
Ea Length/Depth (in.):	1.834
Ea Width (in.):	4.500
Ea Height (in.):	7.375
Wt. Ea. (Lbs.):	0.819
Package Type:	Loose
Product UPC-A Labeled:	Yes

PACKAGING

Case I2of5:	50050169001979
Standard Carton Qty:	25
Min Order Qty:	25



All RACO single-gang, two-gang, 4 In. square, and single gang gangable U.L. listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult U.L. "Fire Resistance Directory" or the U.L. website at www.ul.com

600V

Per UL 514-A, suitable for use without a bonding jumper in circuits up to 600 volts

Revision 1, June 2021



**COMMERCIAL
CONSTRUCTION**
A Division of Hubbell Incorporated (Delaware)

RACO
3902 W. Sample St.
South Bend, IN 46619
574-234-7151
www.hubbell.com/raco/en

