



*Commercial, Industrial
and Residential Electrical Products*

4 In. Square Box, Welded, 2-1/8 In. Deep, Nine 1/2 In. KO's and Five TKO's, TS Bracket, Flush

Catalog #:
8235



FEATURE BENEFIT

Square boxes are used where multiple conductor runs are split into two or more directions to bring power to a number of electrical devices. Built in bracket or supports speeds installation.

PRODUCT FEATURES

- TS style bracket, flush
- Combination screw heads allow quick installation
- Welded construction
- Nine 1/2 In. knockouts and Five TKO knockouts
- UL Listed
- 30.3 cu. in. capacity
- Acceptable in 2-hour fire rated walls

APPLICATIONS

Designed to enclose electrical wiring, switches, receptacles or lighting fixtures. Constructed from 1/16 In. pre-galvanized steel. 8-32 cover mounting screws assembled. Suitable for use without a bonding jumper in circuits up to 600V.

CERTIFICATIONS



PRODUCT SPECIFICATIONS

UPC Number:	050169002353
Ea Length/Depth (in.):	2.402
Ea Width (in.):	4.436
Ea Height (in.):	7.01
Wt. Ea. (Lbs.):	1.016
Package Type:	Loose
Product UPC-A Labeled:	Yes

PACKAGING

Case I2of5:	50050169002358
Standard Carton Qty:	25
Min Order Qty:	25



All RACO single-gang, two-gang, 4 In. square, and single gang gangable U.L. listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult U.L. "Fire Resistance Directory" or the U.L. website at www.ul.com

600V Per UL 514-A, suitable for use without a bonding jumper in circuits up to 600 volts

Revision 1, March 2020



**COMMERCIAL
CONSTRUCTION**
A Division of Hubbell Incorporated (Delaware)

RACO
3902 W. Sample St.
South Bend, IN 46619
574-234-7151
www.hubbell.com/raco/en

