




## 4-11/16 IN. SQUARE WELDED BOXES 2-1/8 IN. WITH CONDUIT KO'S

4-11/16 in. Square Boxes, 2-1/8 in. Deep - Welded with Conduit KO's  
600V, Raised Ground

A26



Catalog #: 8257

### APPLICATIONS

RACO® 4-11/16" Boxes are used for a wide variety of industrial applications where larger sized conductors or wiring devices are needed and more volume is required

### PRODUCT FEATURES

Combination screw heads provide for faster installation  
TKO knockouts allow for design and installation flexibility

### UL LISTED

File E 195978

### COMPLIANCES

600V Per UL 514-A, suitable for use without a bonding jumper in circuits up to 600 volts

### GENERAL PRODUCT INFORMATION

Wiring System: Conduit

### CONFIGURATION

Bracket Type: No Bracket  
Drawn or Welded: Welded  
Raised Ground: Yes  
Side Knockout(s): (12) TKO®  
Bottom Knockouts(s): (1) 1/2 in. & (3) TKO®

### DRAWING DIMENSIONS

Dimension A: 2-1/8 in.

### PRODUCT MEASUREMENTS

Depth: 2-1/8 in.  
Cubic Inches (cm<sup>3</sup>): 42.0 (688.2)  
Wt. Ea. (Lbs.): 1.104  
Product Length (in.): 2.19  
Product Width (in.): 4.69  
Product Height (in.): 4.69

### PACKAGING

Minimum Pack Qty.: 25  
Std. Pkg.: 25  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 110.40  
Ship Carton Length (in.): 21.38  
Ship Carton Width (in.): 7.50  
Ship Carton Height (in.): 9.75  
Ctn Weight (Lbs.): 27.60  
Pallet Qty: 1500  
UPC Number: 050169002575  
I2of5: 50050169002570