




## WELDED GANG BOXES WITH CONDUIT KO'S

Gang Boxes, 2-1/2 in. Deep - Welded with Conduit KO's  
4-Gang

A54



Catalog #: 943

### APPLICATIONS

RACO® Gang boxes are used where a number of wiring devices are to be centrally located  
N/A

### PRODUCT FEATURES

Gang boxes save time in installation, no need to gang boxes together  
Have 3/4" and 1" concentric KO's for use with a wide variety of wiring methods  
Bottom KO pattern, 3-1/2" and 2-3/4" at either end of box  
Accepts two styles of covers, flat and 3/4" raised device cover  
Use low voltage partitions #947 or #949

### UL LISTED

File E195978

### GENERAL PRODUCT INFORMATION

Wiring System: Conduit

### CONFIGURATION

Top & Bottom Knockouts(s): (4) 3/4, (4) 3/4-1 in. Concentric  
Back Knockout(s): (6) 1/2 in. & (4) 3/4 in.  
Gangs: 4  
Side Knockout(s): (4) 3/4-1 in. Concentric

### DRAWING DIMENSIONS

Dimension A: 2-1/2 in.  
Dimension B: 10 in.  
Dimension C: 10-7/16 in.

### PRODUCT MEASUREMENTS

Depth: 2-1/2 in.  
Cubic Inches (cm3): 110.0 (1802.5)  
Wt. Ea. (Lbs.): 2.313  
Product Length (in.): 2.50  
Product Width (in.): 4.50  
Product Height (in.): 10.44

### PACKAGING

Minimum Pack Qty.: 5  
Std. Pkg.: 5  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 231.30  
Ship Carton Length (in.): 11.25  
Ship Carton Width (in.): 9.50  
Ship Carton Height (in.): 7.75  
Ctn Weight (Lbs.): 11.57  
Pallet Qty: 320  
UPC Number: 050169009437  
I2of5: 50050169009432