




WELDED GANG BOXES WITH CONDUIT KO'S

Gang Boxes, 2-1/2 in. Deep - Welded with Conduit KO's
6-Gang

A54



Catalog #: 945

APPLICATIONS

RACO® Gang boxes are used where a number of wiring devices are to be centrally located
N/A

PRODUCT FEATURES

Gang boxes save time in installation, no need to gang boxes together
Have 3/4" and 1" concentric KO's for use with a wide variety of wiring methods
Bottom KO pattern, 3-1/2" and 2-3/4" at either end of box
Accepts two styles of covers, flat and 3/4" raised device cover
Use low voltage partitions #947 or #949

UL LISTED

File E195978

GENERAL PRODUCT INFORMATION

Wiring System: Conduit

CONFIGURATION

Top & Bottom Knockouts(s): (6) 3/4, (6) 3/4-1 in. Concentric
Back Knockout(s): (6) 1/2 in. & (4) 3/4 in.
Gangs: 6
Side Knockout(s): (4) 3/4-1 in. Concentric

DRAWING DIMENSIONS

Dimension A: 2-1/2 in.
Dimension B: 13-5/8 in.
Dimension C: 14-1/16 in.

PRODUCT MEASUREMENTS

Depth: 2-1/2 in.
Cubic Inches (cm3): 150.0 (2458.0)
Wt. Ea. (Lbs.): 3.188
Product Length (in.): 2.50
Product Width (in.): 4.50
Product Height (in.): 14.06

PACKAGING

Minimum Pack Qty.: 1
Std. Pkg.: 1
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 318.80
Ship Carton Length (in.): 4.88
Ship Carton Width (in.): 14.75
Ship Carton Height (in.): 4.00
Ctn Weight (Lbs.): 3.19
Pallet Qty: 144
UPC Number: 050169009451
I2of5: 50050169009456