




## WELDED GANG BOXES WITH CONDUIT KO'S

Gang Boxes, 1-5/8 in. Deep - Welded with Conduit KO's  
6-Gang

A54



Catalog #: 955

### APPLICATIONS

RACO® Gang boxes are used where a number of wiring devices are to be centrally located  
N/A

### PRODUCT FEATURES

Gang boxes save time in installation, no need to gang boxes together  
Have 1/2" and 3/4" concentric KO's for use with a wide variety of wiring methods  
Bottom KO pattern, 3-1/2" and 2-3/4" at either end of box  
Accepts two styles of covers, flat and 3/4" raised device cover  
Use low voltage partitions #947 or #949

### UL LISTED

File E195978

### GENERAL PRODUCT INFORMATION

Wiring System: Conduit

### CONFIGURATION

Top & Bottom Knockouts(s): (16) 1/2-3/4 in. Concentric  
Back Knockout(s): (6) 1/2 in. & (4) 3/4 in.  
Gangs: 6  
Side Knockout(s): (4) 1/2-3/4 in. Concentric

### DRAWING DIMENSIONS

Dimension A: 1-5/8 in.  
Dimension B: 13-5/8 in.  
Dimension C: 14-1/16 in.

### PRODUCT MEASUREMENTS

Depth: 1-5/8 in.  
Cubic Inches (cm3): 98.5 (1614.1)  
Wt. Ea. (Lbs.): 2.450  
Product Length (in.): 1.63  
Product Width (in.): 4.50  
Product Height (in.): 14.06

### PACKAGING

Minimum Pack Qty.: 1  
Std. Pkg.: 1  
Product UPC-A Labeled: No  
Weight (Lbs. Per/C): 245.00  
Ship Carton Length (in.): 20.13  
Ship Carton Width (in.): 2.25  
Ship Carton Height (in.): 5.00  
Ctn Weight (Lbs.): 2.45  
Pallet Qty: 304  
UPC Number: 050169895504  
I2of5: 50050169009555