



Yoke Plate, Rectangular

by ANDERSON
Catalog ID: 976113002

Yoke Plate, Rectangular, Steel, UTS 30,000 lb. YOKE, PLATE RECTANGLE
STL UTS 30K 5/8 IN



* Representative image

Product Details

General

Corona Ring Mounting Provision	4 x 0.500" Cap Screws
Material	Steel
Number of Bolt Holes	0
Series	YPR Series
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate Body	0 lb
Type	Strain Yokes
UPC	096359253426

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Insulator Attachment Holes	0.688 in
Diameter - Pin	0 in
Insulator / Conductor Hole Spacing	18 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Length - Coupling	6 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Thickness	0.625 in
Weight	29.400 lb

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in
Diameter - Conductor Attachment Holes	0.938 in

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscshubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com