



A060804

by Wiegmann
Catalog ID: A060804

N1 Hinged-Cover 6X8X4 Carbon Steel - Gray

Designed for use as surface-mounted junction box, switch box and cutout box.

- Bodies and doors fabricated from 16 gauge steel. 4" depth boxes are furnished with clamp style hinges allowing for removable/replaceable covers. Various sizes of removable concentric knockouts are furnished on all four sides of standard cutout boxes. Mounting holes on back of box.

Product Details

General

Application	Designed for use as surface-mounted junction box, service box, switch box, and cutout box.
Color	Gray
Construction	Spot and Tack Welded
Cover Type	Hinged Cover
Finish Type	Textured
Knockouts	Yes
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Embossed Mounting Holes
Mounting Type	Wall Mount
Type	Enclosure
UPC	786725300600

Dimensions

Actual Height	8.125 in
Actual Width	6.125 in
Depth	4 in
Height	8 in
Weight	4.1 lb
Width	6 in

Conductor Related

Cable Entry	Knock Outs
-------------	------------

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	NEMA 1
UL Listed	Yes