



A121204

by Wiegmann
Catalog ID: A121204

N1 Hinged-Cover 12X12X4 Carbon Steel - Gray

Designed for use as surface-mounted junction box, switch box and cutout box.

- Bodies and doors fabricated from 16 gauge steel. 4" depth boxes are furnished with clamp style hinges allowing for removable/replaceable covers. Various sizes of removable concentric knockouts are furnished on all four sides of standard cutout boxes. Mounting holes on back of box.

Product Details

General

| | |
|-----------------|--|
| Application | Designed for use as surface-mounted junction box, service box, switch box, and cutout box. |
| Color | Gray |
| Construction | Spot and Tack Welded |
| Cover Type | Hinged Cover |
| Finish Type | Textured |
| Knockouts | Yes |
| Listings | UL, CSA |
| Material | Carbon Steel |
| Mounting Method | Embossed Mounting Holes |
| Mounting Type | Wall Mount |
| Type | Enclosure |
| UPC | 786725301607 |

Dimensions

| | |
|---------------|-----------|
| Actual Height | 12.125 in |
| Actual Width | 12.125 in |
| Depth | 4 in |
| Height | 12 in |
| Weight | 9.6 lb |
| Width | 12 in |

Conductor Related

| | |
|-------------|------------|
| Cable Entry | Knock Outs |
|-------------|------------|

Certifications and Compliance

| | |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none">• UL• CSA |
| Nema Rating | NEMA 1 |
| UL Listed | Yes |