



\* Representative image

# Stud Connector, Aluminum

by ANDERSON  
Catalog ID: ADSC11612

Stud Connector, Aluminum, 1-1/8-12 Stud to Cable 0.232-0.575, Straight.  
STUD, AL 1-1/8-14, .232-.575 IN

## Product Details

### General

|                                  |                |
|----------------------------------|----------------|
| Material                         | Aluminum       |
| Material - Clamping Hardware     | Aluminum Alloy |
| Number of Ground Braid Lug Holes | 0              |
| Number of Stud Threads           | 12             |
| Type                             | Stud to Cable  |
| UPC                              | 096359281634   |

### Dimensions

|                           |          |
|---------------------------|----------|
| Angle - Stud to Conductor | 180 °    |
| Base Hole Spacing         | 0 in     |
| Diameter - Base Holes     | 0 in     |
| Diameter - Bolt           | 0 in     |
| Diameter - Inside         | 0 in     |
| Diameter - Stud           | 1.125 in |
| Length - Coupling         | 0 in     |
| Length Before Compression | 0 in     |
| Weight                    | 1.176 lb |

### Electrical Ratings

|  |   |
|--|---|
| Maximum Current Rating Amps Continuous | 0 |
|--|---|

### Conductor Related

|                              |  |
|------------------------------|--|
| Conductor Compatibility      | ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;ACSR-Pigeon-3/0-6/1;ACSR-Penguin-4/0-6/1;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAC-Valerian-250-19 |
| Conductor Diameter - Maximum | 0.575 in   |
| Conductor Diameter - Minimum | 0.232 in   |
| Conductor Diameter Range     | 0.232 - 0.575  |
| Conductor Type               | <ul style="list-style-type: none"> <li>• AAC</li> <li>• ACSR</li> </ul>  |

**For further technical assistance, please contact us**

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)