



* Representative image

Stud Connector, Aluminum

by ANDERSON
Catalog ID: ADSC141612

Stud Connector, Aluminum, 1-1/2-12 Stud to Cable 1.382-1.632, Straight.
STUD, AL 1-1/2-12, 1.382-1.632 IN

Product Details

General

Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Number of Ground Braid Lug Holes	0
Number of Stud Threads	12
Type	Stud to Cable
UPC	096359281788

Dimensions

Angle - Stud to Conductor	180 °
Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Diameter - Stud	1.5 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	2.842 lb

Electrical Ratings

Maximum Current Rating Amps Continuous	0
--	---

Conductor Related

Conductor Compatibility	ACSR-Pheasant-1272-54/19;ACSR-Dipper-1351.5-45/7;ACSR-Martin-1351.5-54/19;ACSR-Bobolink-1431-45/7;ACSR-Plover-1431-54/19;ACSR-Nuthatch-1510.5-45/7;ACSR-Parrot-1510.5-54/19;ACSR-Lapwing-1590-45/7;ACSR-Falcon-1590-54/19;ACSR-Chukar-1780-84/19;AAC-Gladiolus-1510.5-61;AAC-Coreopsis-1590-61;AAC-Cowslip-2000-91
Conductor Diameter - Maximum	1.632 in
Conductor Diameter - Minimum	1.382 in
Conductor Diameter Range	1.382 - 1.632
Conductor Type	<ul style="list-style-type: none"> • AAC • ACSR

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com