



* Representative image

ALRB300CBC

by Acme Electric

Catalog ID: ALRB300CBC

Prop65_Cancer&Reproductive

AC Line Reactor - Three Phase, 240 Volts 6% Z - 480 Volts 3% Z - 600 Volts 2.4% Z, 74 uH, 300 A

- Protects from damaging voltage drop
- Eliminates nuisance tripping
- Reduces surges and spike currents
- Longer life for motors and solid state components

Product Details

General

Inductance	74 uH
Inductance Range	0-150 uH
Max Temperature Rise	115 Degrees Celsius
Motor Power	250 HP
Mounting Hole Width	4.60 in. (11.7 mm)
Primary Voltage	240V / 480V / 600V
Product Category	AC Line Reactor
Reactor Current	300 A
UL Insulation Class	180°C
UPC	047503000496
Winding Material	CU

Dimensions

Height	8.5 in
Length	8 in
Weight	85 lb
Width	10.8 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240/480/600 V

Certifications and Compliance

CSA Standard	C22.2 No 66
UL Standard	UL 506