



34.5kV, 200kV LIW, 900A, ALTD Switch with Loadbuster Hooks.

by CHANCE Utility
Catalog ID: ALTD09200RB

34.5kV, 200kV LIW, 900A, Line Tension Disconnect Switch with Loadbuster Hooks.



* Representative image

Product Details

General

Blade Type	Solid Copper (two blade truss-member)
Color - Insulator	Dark Gray
Contact	Silver, Copper
Insulator Type	ESP™ Polymer
Tension Range	15000 lb
UPC	096359474609

Dimensions

Weight	11.75 lb
--------	----------

Electrical Ratings

Arc Distance - Dry	15.3" (388.6mm)
BIL	200 kV
Creep and Leakage Distance	31.4" (797.6mm)
Current Overload - 8hr Emergency	1080 A
Current Rating	900 A
Dead-Ending Rating - Working Load	15,000 Lbs
Reference Voltage Limit - Minimum	34.5kV
Temperature Rise - Max. at 600A	28°C
Voltage - Maximum	38 kV
Withstand Current - Short Time (1 sec)	25kA, symmetrical
Withstand Current - Short Time (10 cycles)	40kA, assymetrical

Certifications and Compliance

Industry Standard(s)	All Applicable ANSI/IEEE Standards
----------------------	------------------------------------

Logistics

Pallet Quantity	24 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscshubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com