

Tee, Aluminum Bolted

by ANDERSON
Catalog ID: ATCF21301

Tee, Aluminum Bolted, Cable to Flat, 1824-2 Main to 3 in, 4 hole Flat Tap.
TEE, AL BOLT, 1.824-2.0 IN, D PAD



* Representative image

Product Details

General

Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Number of Ground Braid Lug Holes	0
Number of Pad Holes	4
Type	Tee, Bolted
UPC	096359287155

Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	4.410 lb
Width - Flat Bar Tap	3 in

Electrical Ratings

Maximum Current Rating Amps Continuous	0
--	---

Conductor Related

Conductor Compatibility	ACSR-Joree-2515-76/19
Conductor Diameter (Main) - Maximum	2 in
Conductor Diameter (Main) - Minimum	1.824 in
Conductor Diameter (Main) Range	1.824 - 2

Conductor Type

- AAC
- ACSR

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com