

18X16X10 POLYCARBONATE ENCLOSURE WITH SOLID DOOR, KEY LOCK AND CORD GRIP



The AccelTex Solutions polycarbonate enclosure protects any enterprise-class AP from environmental threats and tampering. Purpose built for enterprise applications, this aesthetically pleasing enclosure is inconspicuous in an indoor application and durable enough to provide NEMA 6P protection in an outdoor environment.

Part Number: ATS-181610P-S-K-CG-BBP



MECHANICAL SPECIFICATIONS

Size: 18" H x 16" W x 10" D (457.2 mm H x 406.4 mm W x 254 mm D)

Weight: 11.2 lbs (5.08 kg)

Color: Light Grey

Material: Polycarbonate

Door Type: Solid

Lock Type: Key Lock Plus Latch with Integrated Pad Lockable Hasp

Antenna Connection Holes: 0

Hole Size: None Cord Grip: Yes

Equipment Installation: Blank Backplate Enclosure Installation: Mounting Feet



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor

Environmental Protection: NEMA 6P, 4X, 4, 3R, 122; IP68 Operating Temperature: -20 to 240°F (-28 to 115°C)



WARRANTY

2 Year Limited Warranty