



24X24X10 POLYCARBONATE ENCLOSURE WITH CLEAR DOOR, KEY LOCK AND CORD GRIP

The AccelTex Solutions polycarbonate enclosure protects any enterprise-class AP from environmental threats and tampering. Purpose built for enterprise applications, this aesthetically pleasing enclosure is inconspicuous in an indoor application and durable enough to provide NEMA 6P protection in an outdoor environment.

Part Number: ATS-242410P-C-K-CG-BBP



MECHANICAL SPECIFICATIONS

Size: 24" H x 24" W x 10" D (609.6 mm H x 609.6 mm W x 254 mm D) Weight: 34 lbs (15.42 kg) Color: Light Grey Material: Polycarbonate Door Type: Clear Lock Type: Key Lock Plus Latch with Integrated Pad Lockable Hasp Antenna Connection Holes: 0 Hole Size: None Cord Grip: Yes Equipment Installation: Blank Backplate Enclosure Installation: Integrated Wall Flange

ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor Environmental Protection: NEMA 6P, 4X, 4, 3R, 122; IP68 Operating Temperature: -20 to 240°F (-28 to 115°C)

WARRANTY

2 Year Limited Warranty

The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. All AccelTex Solutions products are sold pursuant to the AccelTex Solutions Terms and Conditions of Sale. © 2017 AccelTex Solutions. All Rights Reserved. AccelTex, AccelTex Solutions, the AccelTex Solutions Logo and other marks are trademarks or registered trademarks of AccelTex Solutions. Other products or service names may be the property of third parties.

1.888.406.8906 SALES@ACCELTEX.COM