

2.4/5 GHZ 4/6 DBI WHITE ARTICULATING OMNI-**ANTENNA WITH N-STYLE** ATS-ID90RD-245-46-1NP-IC-W



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.5/4.9-5.85 GHz Gain: 4/6 dBi Polarization: Vertical Horizontal Beamwidth: 360° VSWR: Max 2.0



MECHANICAL SPECIFICATIONS

Dimensions: 8.03" x 0.28" x \phi1.65" (207x7x \phi42mm) Articulation: 90° Connector: N-Style Plug Installation: Direct Connect Color: White



ENVIRONMENTAL SPECIFICATIONS




Installation Environment: Indoor IP Rating: IP66

2 Year Limited Warranty



HORIZONTAL






The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. All AccelTex Solutions products are sold pursuant to the AccelTex Solutions Terms and Conditions of Sale. © 2023 AccelTex Solutions. All Rights Reserved. AccelTex, AccelTex Solutions, the AccelTex Solutions Logo and other marks are trademarks or registered trademarks of AccelTex Solutions. Other products or service names may be the property of third parties.

1.888.406.8906 SALES@ACCELTEX.COM



2.4/5 GHZ 4/6 DBI WHITE ARTICULATING OMNI ANTENNA WITH N-STYLE ATS-ID90RD-245-46-1NP-IC-W



The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. All AccelTex Solutions products are sold pursuant to the AccelTex Solutions Terms and Conditions of Sale. © 2023 AccelTex Solutions. All Rights Reserved. AccelTex, AccelTex Solutions, the AccelTex Solutions Logo and other marks are trademarks or registered trademarks of AccelTex Solutions. Other products or service names may be the property of third parties.

1.888.406.8906 SALES@ACCELTEX.COM