

# 2.4/5 GHZ 13 DBI 6 ELEMENT INDOOR/OUTDOOR HIGH DENSITY PATCH ANTENNA WITH N-STYLE ATS-OHDP-245-1312-6NJ-IC



# **ELECTRICAL SPECIFICATIONS**

Frequency Range: 2.4-2.5 / 4.9-5.85 GHz

Gain: 13/12 dBi

Polarization: 3 Vertical / 3 Horizontal Horizontal Beamwidth: 33° / 34° Vertical Beamwidth: 33° / 33°

VSWR: <2.0:1

Isolation: > 20 dB Impedance: 50Ω DC Grounded

Max Input Power: 100 W





## **MECHANICAL SPECIFICATIONS**

Dimensions: 19.29"x 19.29"x 1.38" (490x490x35mm)

Weight: 1.3 lbs. (0.6 kg) Radome Material: ASA Connector: N-Style Jack Number of Connectors: 6



#### **ENVIRONMENTAL SPECIFICATIONS**

Installation Environment: Indoor/Outdoor

Operating Temperature: -40 to 149°F (-40 to 65°C)

IP Rating: IP66

WARRANTY

2 Year Limited Warranty



### **2.4 GHZ**

#### 5 GHZ

