

# 2.4/5 GHZ 4/7 DBI 4 ELEMENT INDOOR/OUTDOOR PATCH ANTENNA WITH RPTNC ATS-OP-245-47-4RPTP-36



# **ELECTRICAL SPECIFICATIONS**

Frequency Range: 2.4-2.5/4.9-5.85 GHz

Gain: 4 / 7 dBi Polarization: Vertical

Horizontal Beamwidth: 99°/58° Vertical Beamwidth: 65°/40° VSWR: < 2.0:1 Isolation: > 20dB Impedance: 50Ω

Lightning Protection: DC Grounded

Max Input Power: 100W





# **MECHANICAL SPECIFICATIONS**

Dimensions: 5.5"x 4.7"x 1.5" (140x120x39mm)

Weight: 0.9 lb (0.4 kg)

Mounting: Threaded Bolt w/ Nut

& Articulating Wall/Pole Mount (included) Installation Hole Diameter: 1" (25mm) Pole Mount Diameter: 2" (50mm) Radome Material: ASA Connector: RPTNC Number of Leads: 4

Cable Length: 36" (910 mm)

Cable Type: RG58



# **ENVIRONMENTAL SPECIFICATIONS**

Installation Environment: Indoor/Outdoor

Operating Temperature: -40 to 149°F (-40 to 65°C)

Wind Velocity: 130 mph (209 km/h)

IP Rating: IP66

### **WARRANTY**


2 Year Limited Warranty



# 2.5 GHZ

H-Plane

## 5 GHZ



V-Plane